



CERT

DVGW type examination certificate

DVGW-Baumusterprüfzertifikat

DW-8501CT0368

Registration Number
Registriernummer

Field of Application <i>Anwendungsbereich</i>	products of water supply <i>Produkte der Wasserversorgung</i>
Owner of Certificate <i>Zertifikatinhaber</i>	Viega GmbH & Co. KG Viega Platz 1, D-57439 Attendorn
Distributor <i>Vertreiber</i>	Viega GmbH & Co. KG Viega Platz 1, D-57439 Attendorn
Product Category <i>Produktart</i>	Installation systems and system joints (PN 10): drinking water installation system (8501)
Product description <i>Produktbezeichnung</i>	Circulation Line
Model <i>Modell</i>	Smartloop-Inliner
Test reports <i>Prüfberichte</i>	Laboratory control test: 12 7804-23-01-01-IB from 02.10.2023 (MPM) Type testing: P000210660-1 from 08.02.2023 (KIW) Type testing: 120005092 from 04.09.2018 (MPM) UBA Guideline/BWGL: Z-346655-21-Hy112 from 31.01.2023 (WHY) UBA Guideline/BWGL: Z-341504-21-Hy101 from 25.03.2021 (WHY)
Test basis <i>Prüfgrundlagen</i>	DVGW CERT ZP 8500 (23.05.2022) DVGW W 534-(P) (01.07.2015)- partially UBA BWGL-Metalle (11.01.2023) UBA KTW-BWGL (07.03.2022)
Date of Expiry / File No. <i>Ablaufdatum / Aktenzeichen</i>	04.09.2028 / 23-0477-WNV

70026 04 A DE

26.03.2024 LE A-1/2

Date, Issued by, Sheet, Head of Certification Body
Datum, Bearbeiter, Blatt, Leiter der Zertifizierungsstelle



DVGW CERT GmbH
Zertifizierungsstelle

Josef-Wirmer-Str. 1-3
53123 Bonn

Tel. +49 228 91 88 - 888
Fax +49 228 91 88 - 993

www.dvgw-cert.com
info@dvgw-cert.com

Type <i>Typ</i>	Technical Data <i>Technische Daten</i>	Remarks <i>Bemerkungen</i>
Smartloop-Inliner	Nominal diameter: 28 mm	for "Profipress", "Sanpress" and "Sanpress Inox"
Smartloop-Inliner	Nominal diameter: 32 mm	for "Raxofix" and "Viega Smartpress"
Smartloop-Inliner	Nominal diameter: 35 mm	for "Profipress", "Sanpress" and "Sanpress Inox"

Hints of Utilization / Remarks

Verwendungshinweise / Bemerkungen

The drinking water installation systems "Profipress", "Sanpress" and "Sanpress Inox" can be expanded with the "Smartloop inline technology" to a circulation line.

Press fittings to use:

Smartloop end closing piece, type M-MM/M-MK

Smartloop adapter, type M-MM/M-MK

Smartloop connecting piece, type M-MM

Smartloop repair nipple; type M-MK

Material of the press fittings: Red brass CC499K or silicon bronze CC246E/CuSi4Zn9MnP

Pressing tools to use:

Pressing tools from Viega Technology GmbH & Co.KG, D-57429 Attendorn

DW